


Spherical Collar Nuts



- ▶ Available in case hardened carbon steel or stainless steel
- ▶ Spherical collar nuts can be used with the bottom half of Morton's spherical washers for self-alignment.

Low Carbon Steel PART #	Stainless Steel PART #	Thread				
		A	B	C	D	E
SCN-0	SCN-0SS	1/4-20	1/2	5/8	5/16	3/32
SCN-00	SCN-00SS	5/16-18	9/16	3/4	3/8	3/32
SCN-1	SCN-1SS	3/8-16	11/16	7/8	1/2	1/8
SCN-9	-	7/16-14	3/4	1	9/16	5/32
SCN-2	SCN-2SS	1/2-13	7/8	1-1/8	11/16	5/32
SCN-3	SCN-3SS	5/8-11	1-1/16	1-3/8	13/16	3/16
SCN-4	SCN-4SS	3/4-10	1-1/4	1-5/8	1	1/4
SCN-5	SCN-5SS	7/8-9	1-7/16	1-7/8	1-1/8	1/4
SCN-6	SCN-6SS	1"-8	1-5/8	2	1-1/4	1/4
SCN-7	SCN-7SS	1-1/8-7	1-13/16	2-1/4	1-1/4	1/4
SCN-8	-	1-1/4-7	2	2-5/8	1-1/4	1/4




Acorn Nuts



- ▶ Available in case hardened steel or stainless steel
- ▶ Excellent for protecting exposed threads

INCH

Low Carbon Steel PART #	Stainless Steel PART #	Thread			Thread Depth
		A	Hex	C	
AN-6	AN-6SS	1/4-20	5/8	5/8	1/2
AN-0	AN-0SS	5/16-18	5/8	5/8	1/2
AN-1	AN-1SS	3/8-16	3/4	3/4	19/32
AN-2	AN-2SS	1/2-13	7/8	15/16	3/4
AN-3	AN-3SS	5/8-11	1-1/16	1-3/16	15/16
AN-4	AN-4SS	3/4-10	1-1/4	1-3/8	1-3/32
AN-5	AN-5SS	7/8-9	1-7/16	1-5/8	1-9/32



METRIC

Low Carbon Steel PART #	Stainless Steel PART #	Thread			Thread Depth
		A	Hex	C	
AN-206	AN-206SS	M6 x 1.0	15mm	16mm	9.5mm
AN-208	AN-208SS	M8 x 1.25	16	16	9.5
AN-210	AN-210SS	M10 x 1.5	19	19	12
AN-212	AN-212SS	M12 x 1.75	22	24	15
AN-216	AN-216SS	M16 x 2.0	30	30	20